

HOLEX**Pair of gloves Pro Cut D / Protector, Glove size: 8****Order data**

Order number	094603 8
GTIN	4062406572198
Item class	02H

Description**Version:**

HOLEX Pro Cut D. Seamless knitted cut-resistant gloves for precise and general-purpose activities and protection against high cut hazards. With PU nitrile foam coating and very good fit and dexterity. With reinforced thumb joint for longer life. Ideal for use in both dry and oily working conditions. **18 gauge knitted technology.**

With additional protectors for the backs of the hands to protect against minor blows and impacts.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Protection category	Category II
Glove size	8
Type of glove	Cut-resistant gloves

Contents	12
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	Shock protection
Glove characteristics	DMF-free
Knitted technology	18G
Drying	air dry
EN 388	4X43D
Backing material	HPPE
Coating	water-based PU/nitrile
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey
Length	255 mm
Application	reusable
AQL	G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor.
Cut protection class	D
Type of product	Cut-resistant gloves