

**TMSERROR, Type: GBH18V45C**

---

**Order data**

Order number	075515 GBH18V45C
GTIN	3165140915427
Item class	03B

---

**Description****Version:**

**18-V cordless hammer drill with SDS-plus tool mounting** and brushless motor.

- **Overload clutch to protect both user and machine.**
- **Reversible.**
- **Extremely sturdy: Electronic Motor Protection switches off the motor if it is overloaded. Fully operational even after a drop test from 2 m on to concrete.**
- **Lighter than comparable products with cables thanks to the highly optimised drive train – also with ProCORE18V 12.0Ah.**
- **Comfort while working thanks to Lock-on Button for continuous chisel work.**
- **Maximum power thanks to BITURBO technology.**
- **Precise work results thanks to speed setting for variable speeds.**
- **Improved visibility due to LED work light.**
- **Kick Back Control to reduce risks from sudden tool reactions.**
- **Equipped with Soft-Start, ASC and EPC for top user protection.**
- **Flexible work thanks to individual configuration depending on the application, using the Bosch My Tools app.**

**Supplied with:**

Including additional handle, connectivity module, machine cloth and case.

**Note:**

Suitable carbide hammer drills can be found from No. 787000. Suitable spare batteries and chargers can be found under No. 073851 – 073866.

---

**Technical description**

---

maximum twist drill size Ø in concrete	45 mm
Weight	8 kg
Impact energy	12.5 J
Battery voltage	18 V
Tool arbor shape	SDS Max
Type of rechargeable battery	Lithium-ion
maximum hammer rate	2760 min <sup>-1</sup>
Manufacturer's designation	GBH 18V-45 C
Packaging	Carrying case
Power supply	Rechargeable battery-powered
Number of rechargeable batteries contained	2
Shank	SDS Max
Type of product	Hammer drill

## Accessories

Battery starter set ProCore Battery type, battery voltage C18 V	073865 C18
Battery charger Type GAL18V6-80	073866 GAL18V6-80
Li-ion battery ProCore Battery type, battery voltage C18 V	073857 C18
Battery charger Type 1880CV	073866 1880CV
Battery charger Type GAL18160C	073866 GAL18160C