

**Pair of gloves Pro Cut D, Glove size: 9****Order data**

Order number	094602 9
GTIN	4062406572150
Item class	02H

Description**Version:**

HOLEX Pro Cut D. Seamless knitted cut-resistant gloves for precise and general-purpose activities and protection against high cut hazards. With PU nitrile foam coating and very good fit and dexterity. With reinforced thumb joint for longer life. Ideal for use in both dry and oily working conditions. **18 gauge knitted technology.**

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Protection category	Category II
Type of glove	Cut-resistant gloves
Glove size	9
Contents	12

Glove characteristics	Reinforced crook of the thumb
Glove characteristics	DMF-free
Knitted technology	18G
Drying	air dry
EN 388	4X43D
Backing material	HPPE
Coating	water-based PU/nitrile
Coating variant	The palms of the hands
Application range	Precision
Colour	black / grey
Length	255 mm
Application	reusable
AQL	G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor.
Cut protection class	D
Type of product	Cut-resistant gloves