

HOLEX**Pair of gloves Pro Cut D / Protector, Glove size: 7****Order data**

| | |
|--------------|---------------|
| Order number | 094603 7 |
| GTIN | 4062406572181 |
| Item class | 02H |

Description**Version:**

HOLEX Pro Cut D. Seamless knitted cut-resistant gloves for precise and general-purpose activities and protection against high cut hazards. With PU nitrile foam coating and very good fit and dexterity. With reinforced thumb joint for longer life. Ideal for use in both dry and oily working conditions. **18 gauge knitted technology.**

With additional protectors for the backs of the hands to protect against minor blows and impacts.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|---------------------|----------------------|
| Protection category | Category II |
| Type of glove | Cut-resistant gloves |
| Glove size | 7 |

| | |
|-----------------------|--|
| Contents | 12 |
| Glove characteristics | Reinforced crook of the thumb |
| Glove characteristics | Shock protection |
| Glove characteristics | DMF-free |
| Knitted technology | 18G |
| Drying | air dry |
| EN 388 | 4X43D |
| Backing material | HPPE |
| Coating | water-based PU/nitrile |
| Coating variant | The palms of the hands |
| Application range | All-round |
| Colour | black / grey |
| Length | 255 mm |
| Application | reusable |
| AQL | G-II 1.0 for critical, G-II 2.5 for major, G-II 4.0 for minor. |
| Cut protection class | D |
| Type of product | Cut-resistant gloves |