

**Hammer drill, Type: GBH221****Order data**

Order number	075510 GBH221
GTIN	4059952569635
Item class	03B

Description**Version:**

Sturdy hammer drill with **SDS-plus arbor** and high drill feed rate.

- **Overload clutch to protect both user and machine.**
- **Stepless speed control for responsive starts to drilling.**
- **Versatile application possibilities using the chisel function (zero rotation).**
- **Reversible, for releasing jammed drills.**

Supplied with:

With additional handle, machine cloth. Supplied with 210 mm depth stop and carrying case.

Note:

Suitable carbide hammer drills can be found from No. 787000. Suitable spare batteries and chargers can be found under No. 073851 – 073866.

Technical description

maximum twist drill size \varnothing in concrete	20 mm
Power supply	Battery-powered
Tool arbor shape	SDS-Plus
Power consumption	650 W

Shank	SDS Plus
Impact energy	2 J
maximum twist drill size Ø in wood	30 mm
Weight	2.3 kg
maximum twist drill size Ø in steel	13 mm
Packaging	Carrying case
Manufacturer's designation	GBH 2-21 D
maximum vibration to EN	13.5 m/s ²
Type of product	Hammer drill