



GWX angle grinder without battery, Type: 18V15C



Order data

Order number	077011 18V15C
GTIN	4059952512037
Item class	03C

Description

Version:

- **Easy and quick:** Easy change of angle grinder accessories without any parts that could be lost or need for additional tools.
- **Additional wrench no longer required.**
- **Comprehensive:** Huge range of angle grinders and accessories with complete backwards compatibility.
- **Maximum convenience** thanks to completely tool-less and quick accessory replacement.
- **Reliable:** Directional accessories can no longer be mounted incorrectly thanks to the innovative X-LOCK system. Maximum user protection thanks to acoustic signal upon correct mounting.
- **Clean working without annoying scratches!** Less prominent and fewer scuffs with X-Lock angle grinders.

Cordless angle grinder with BITURBO brushless technology with X-Lock.

- **Has the same amount of power as a corded device with 1000 to 1800 watts.**
- **Ensures quicker cutting and more metal removal than with previous cordless grinders.**
- **Increased safety thanks to intelligent braking system, kick-back and drop control.**

Supplied with:

Supplied with additional vibration control handle, safety guard, L-BOXX 136.

Note:

Suitable ProCore 18-V batteries and starter sets can be found under No. 073857 size C18 and No. 073865 size C18

Technical description

maximum disc Ø	125 mm
----------------	--------

Number of rechargeable batteries contained	0
Power supply	Battery-powered
Packaging	Modular case (L-Boxx)
Weight	2.3 kg
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Kick-back stop	yes
Manufacturer's designation	GWX 18V-15 C
Motor design	brushless motor
suitable battery - supplier / battery type / voltage	Bosch 18 V
Special features	BITURBO; Kickback Control; Drop Control
Restart block	yes
Speed range	9800 min ⁻¹
Toolholder	X-LOCK system
Series	X-LOCK system
Type of product	Angle grinder

Accessories

Battery starter setProCore Battery type, battery voltage C18 V	073865 C18
Battery charger Type GAL18160C	073866 GAL18160C
Li-ion batteryProCore Battery type, battery voltage C18 V	073857 C18
Battery charger Type GAL18V6-80	073866 GAL18V6-80
Battery charger Type 1880CV	073866 1880CV