



## Cordless angle grinder GWS, Type: 18V15C



### Order data

Order number	077120 18V15C
GTIN	3165140964555
Item class	03C

### Description

#### Version:

- Thanks to the new BITURBO technology, 50% faster cutting and metal removal. Equivalent to the performance of an angle grinder with cable.
- Increased safety thanks to intelligent braking system, soft start, kick-back and drop control.
- Setting of individual speed settings with user interface and Bluetooth connectivity.
- Possibility to retrofit the connectivity module.

#### Supplied with:

Without rechargeable battery and charger, including safety guard, mounting flange, clamping nut, additional handle.

#### Note:

See No. 073854 and No. 073866 for suitable spare batteries and chargers. Suitable ProCORE 18-V batteries and starter sets can be found under No. 073857 size C18 and No. 073865 size C18.

### Technical description

maximum cutting depth	34 mm
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Bosch 18 V
Battery voltage	18 V
maximum disc Ø	125 mm
Soft start	no

Manufacturer's designation	GWS 18V-15 C
Type of rechargeable battery	Lithium-ion
Overload protection	yes
Kick-back stop	yes
Packaging	Modular case (L-Boxx)
maximum vibration to EN	4 m/s <sup>2</sup>
Weight without battery	2.2 kg
Number of rechargeable batteries contained	0
Restart block	yes
Motor design	brushless motor
Dead man's circuit	no
Weight	2.2 kg
maximum speed	9800 min <sup>-1</sup>
App link	OneKey
Type of product	Angle grinder

---

## Accessories

Battery starter setProCore Battery type, battery voltage C18 V	073865 C18
Li-ion batteryProCore Battery type, battery voltage C18 V	073857 C18