

AEG

Cordless drill / driver, Type: BS18SBL2



Order data

Order number	070222 BS18SBL2
GTIN	
Item class	07A

Description

Version:

AEG – Cordless drill / driver

- **Sturdy and handy cordless 2-speed drill / screwdriver, reversible.**
- **FIXTEC quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**
- **LED illumination of the working area.**

Brushless **subcompact** motor with up to 65 Nm of torque, 24-step torque adjustment.

Standard:

- **Sturdy and handy cordless 2-speed drill / driver, reversible.**
- **FIXTEC quick-change chuck with spindle lock.**
- **Handle with Softgrip coating for comfortable use.**

Supplied with:

Supplied with 2 pcs. 18 V / 2.0 Ah battery, charger, transport case.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073820 and No. 073846 – No. 073848 for suitable replacement batteries and chargers. Suitable chargers and starter sets can be found under No. 073841 and No 073844.

Technical description

Battery voltage	18 V
maximum twist drill size Ø in wood	40 mm
Motor design	Brushless subcompact motor
typical application	Strong
Type of rechargeable battery	Lithium-ion
Quick-clamping chuck range	1.5 mm
Manufacturer's designation	BS 18 SBL2
Power supply	Rechargeable battery-powered
maximum speed 1st speed	0 min ⁻¹
Weight	1.3 kg
suitable battery - supplier / battery type / voltage	AEG type B 18 V
maximum twist drill size Ø in steel	13 mm
maximum vibration to EN	<2.5 m/s ²
Battery capacity	2 A·h
maximum torque hard	65 N·m
Number of rechargeable batteries contained	2
Packaging	Carrying case
maximum speed 2nd speed	1750 min ⁻¹
Type of product	Drill/driver
USP1	18V
USP2	FIXTEC quick-change chuck, with softgrip