



Cordless impact wrench / impact driver, Type: M18FMT2F12



Order data

Order number	074010 M18FMT2F12
GTIN	4058546346416
Item class	03L

Description

Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques.

- **Compact design.**
- **Stage 4 for an optimum mix of power and precision when undoing screws.**

Version of the advertising text:

Robust and **powerful FUEL™ cordless impact screwdriver** with **brushless POWERSTATE™ EC motor** for long motor service life and high energy efficiency.

Note:

For matching spare batteries and accessories see from No. 073808.

Technical description

maximum torque 4th setting	47 Nm
Number of rechargeable batteries contained	2
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum torque 3rd step	745 Nm
maximum torque 2nd step	610 Nm
Number of impacts 2nd stage	0 - 2100 min ⁻¹
Tool arbor size	1/2 in
Weight	6.3 kg
maximum screw Ø (8.8 - 12.9)	M22
Tool arbor drive profile	External square drive
typical application	Heavy Duty
Packaging	Modular case (HD=Heavy Duty)
Type of rechargeable battery	Lithium-ion
Battery voltage	18 V
Number of impacts 3rd stage	0 - 3100 min ⁻¹
Number of impacts 1st stage	0 - 900 min ⁻¹
maximum torque 1st step	475 Nm
Manufacturer's designation	M18FMT2F12
Power supply	Rechargeable battery-powered
Battery capacity	5 Ah
Type of product	Impact wrench

Accessories

Battery charger Type M1218FC	073840 M1218FC
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218C	073840 M1218C