



### Impact wrench 18 V, cordless impact wrench



#### Order data

Order number	074010 M18FIW2F12
GTIN	4058546346355
Item class	03L

#### Description

##### Version:

Robust and **powerful FUEL™ cordless impact wrench** with **brushless POWERSTATE™ EC motor**, for long motor service life and high energy efficiency. Sturdy **metal gearbox casing** and ergonomic **central handle with soft-grip coating**. Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. **REDLINK PLUS™ electronics** – for unique power management:

- **With system communication between the drive machine and battery.**
- **With overload protection for longer working life of the battery, motor, and gearbox.**

DRIVE CONTROL™ permits quick switching between the 4 available settings with different speeds and torques. **18 V / 5.0 Ah compact cordless impact driver** with only 124 mm overall length.

- **Compact design.**
- **Stage 4 for an optimum mix of power and precision when undoing screws.**

##### Supplied with:

Supplied with 2× Li-ion batteries, charger, HD box, belt clip.

##### Note:

See No. 073801 – No. 073840 for suitable batteries and chargers.

#### Technical description

typical application	Strong
Number of impacts 3rd stage	0 - 3400 min <sup>-1</sup>
Number of impacts 1st stage	0 - 1000 min <sup>-1</sup>
Weight	5.9 kg
maximum torque 1st step	102 Nm
Number of impacts 2nd stage	0 - 2400 min <sup>-1</sup>
maximum screw Ø (8.8 - 12.9)	ASCD18-300W2
maximum torque 3rd step	339 Nm
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum torque 4th setting	34 Nm
Battery voltage	18 V
Packaging	Modular case (HD=Heavy Duty)
Manufacturer's designation	M18 FIW2F12
maximum torque 2nd step	203 Nm
Tool arbor drive profile	External square drive
Number of rechargeable batteries contained	2
Tool arbor size	1/2 in
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Battery capacity	5 Ah
Type of product	Impact wrench

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/074010-M18FIW2F12>