

**Garant****Polishing point 600 grit (orange) ultra-fine, Head Ø×length: 6X10mm****Order data**

Order number	551924 6X10
GTIN	4062406572563
Item class	51E

**Description****Version:**

Polishing points with **standard aluminium oxide (A)** in resilient rubber bonding.

**GARANT polishing points** are characterised by long service life and quick production of fine, even surface finishes. Finest polishing grades or surfaces right up to mirror finish can be achieved, depending on the version used. GARANT polishing points can be profiled using dressing sticks.

**Application:**

**For fine abrasion and polishing of steel, stainless and acid-resistant steel, high-temperature materials and non-ferrous metals.** Polishing grinding points do not clog even when used on materials prone to clogging. For matt finish or application of visual effects on stainless containers etc. **Due to resilient bonding of abrasive grit a very fine polish is achieved.**

Not suitable for sharp edges and rough surfaces.

**Technical description**

Head Ø	6 mm
Shank Ø	3 mm

Grit	600
Shape description	cylindrical
recommended circumferential speed	10 - 15 m/s
Head length	10 mm
Grinding media	Standard aluminium oxide (A)
Grinding medium code	ZC
Colour	white
Type of product	Polishing points

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
CuZn	suitable		
dry	suitable		