



Angle grinder Cordless, Type: M18FSAGV



Order data

Order number	077105 M18FSAGV
GTIN	4058546360566
Item class	03L

Description

Version:

Cordless angle grinder 115mm with POWERSTATE™ motor (brushless) for very heavy-duty use. The REDLINK PLUS™ electronics offers advanced digital overload protection for machine and battery and delivers constant power even under load. With dead man's switch.

Supplied with:

Without battery, without charger. With cardboard box.

Note:

Suitable starter set can be found from No. 073826.

Technical description

maximum disc Ø	115 mm
Restart block	yes
Power supply	Battery-powered
Dead man's circuit	yes
Number of rechargeable batteries contained	0
maximum vibration to EN	2.1 m/s ²
Motor design	Brushless motor
Speed range	8500 min ⁻¹

Packaging	Modular case (HD=Heavy Duty)
Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
Overload protection	yes
Manufacturer's designation	M18 FSAGV115XPDB-0
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum cutting depth	28 mm
Weight	2.7 kg
Type of product	Angle grinder