



Angle grinder Cordless, Type: M18FSAGDB



Order data

Order number	077140 M18FSAGDB
GTIN	4058546346263
Item class	03L

Description

Version:

18 V / 5.0 Ah FUEL™ Milwaukee cordless angle grinder:

- **long-life brushless motor, spindle locking, quick adjustment of the safety guard.**
- **Integral FIXTEC quick-release system for changing discs without using tools.**

Supplied with:

Supplied with charger, safety guard, 2 dust-protection grilles, clamping set, anti-vibration handle, HD box.

Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

Technical description

Packaging	Modular case (HD=Heavy Duty)
maximum cutting depth	33 mm
maximum vibration to EN	3.4 m/s ²
Battery capacity	5 Ah
Overload protection	yes
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2

Battery voltage	18 V
Restart block	yes
Kick-back stop	no
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
maximum speed	8500 min ⁻¹
Soft start	yes
maximum disc Ø	125 mm
Weight	2.7 kg
Manufacturer's designation	M18FSAGDB
Dead man's circuit	yes
Series	FUEL
Type of product	Angle grinder