



## Angle grinder Cordless, Type: M18FSAGB



### Order data

Order number	077140 M18FSAGB
GTIN	4058546346218
Item class	03L

### Description

#### Version:

18 V / 5.0 Ah FUEL™ Milwaukee cordless angle grinder:

- **long-life brushless motor, spindle locking, quick adjustment of the safety guard.**
- **Integral FIXTEC quick-release system for changing discs without using tools.**

#### Supplied with:

Supplied with charger, safety guard, 2 dust-protection grilles, clamping set, anti-vibration handle, HD box.

#### Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

### Technical description

maximum disc Ø	125 mm
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Dead man's circuit	no

Manufacturer's designation	M18 ONEFSAG125XPDB-502X
Restart block	yes
maximum speed	8500 min <sup>-1</sup>
Type of rechargeable battery	Lithium-ion
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum vibration to EN	3.4 m/s <sup>2</sup>
Weight	2.5 kg
maximum cutting depth	34 mm
Battery voltage	18 V
Soft start	yes
Overload protection	yes
Battery capacity	5 Ah
Packaging	Modular case (HD=Heavy Duty)
Kick-back stop	no
App link	OneKey
Series	FUEL
Type of product	Angle grinder