



Cordless hammer drill without battery, charger or case, Type: M18FHPX



Order data

Order number	075532 M18FHPX
GTIN	4058546346881
Item class	03L

Description

Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **SDS plus chuck.**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**
- **FIXTEC tool quick-change system for switching between the SDS-Plus chuck and the quick-release metal drill chuck, without using tools.**
- **Zero rotation for easy chisel work.**
- **Safety clutch protects user and machine if the drill jams.**
- **AVS anti-vibration system.**

Supplied with:

Zero-speed version – without battery, charger and case.

Note:

Suitable carbide hammer drills can be found from No. 787000. See from No. 073808 and No. 073840 for suitable replacement batteries and chargers.

Technical description

maximum twist drill size \varnothing in concrete	30 mm
Manufacturer's designation	M18ONE FPHX

suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
maximum twist drill size Ø in steel	13 mm
Packaging	Modular case (HD=Heavy Duty)
Shank	SDS Plus
Impact energy	4.2 J
maximum vibration to EN	8.6 m/s ²
Number of rechargeable batteries contained	0
maximum twist drill size Ø in wood	30 mm
maximum hammer rate	4600 min ⁻¹
Weight	5.2 kg
Speed range	0 - 800 min ⁻¹
Tool arbor shape	SDS-Plus
Quick-clamping chuck range	1.5 - 13 mm
Type of product	Hammer drill

Accessories

Battery charger Type M1218SC	073840 M1218SC
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218C	073840 M1218C
Battery starter set Type M18NRG5	073839 M18NRG5
Battery charger Type M1418C6	073840 M1418C6