



Cordless hammer drill, Type: M18FHX



Order data

Order number	075530 M18FHX
GTIN	4058546346973
Item class	03L

Description

Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**
- **18 V / 5.0 Ah Red Li-ion cordless hammer drill** with brushless POWERSTATE™ EC motor, optimised for drilling in concrete and masonry. Redlink Plus™ electronics – overload protection for long working life of the battery, motor and gearbox.
- **FIXTEC tool quick-change system for switching between the SDS-Plus chuck and the quick-release metal drill chuck, without using tools.**
- **Zero rotation for easy chisel work.**
- **Safety clutch protects user and machine if the drill jams.**
- **AVS anti-vibration system.**

Supplied with:

Supplied with FIXTEC SDS-Plus adapter, quick-change chuck 1.5 – 13 mm, additional handle with depth stop, quick charger, 2 pcs. 18 V battery, carrying case.

Note:

Suitable carbide hammer drills can be found from No. 787000. See from No. 073808 and No. 073840 for suitable replacement batteries and chargers.

Technical description

suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
maximum vibration to EN	8.9 m/s ²
Shank	SDS Plus
Speed range	0 - 1330 min ⁻¹
maximum twist drill size Ø in concrete	26 mm
maximum twist drill size Ø in steel	13 mm
Impact energy	2.5 J
maximum twist drill size Ø in wood	28 mm
Manufacturer's designation	M18ONEFHX-552X
Battery voltage	18 V
maximum hammer rate	4800 min ⁻¹
Battery capacity	5.5 Ah
Number of rechargeable batteries contained	2
Tool arbor shape	SDS-Plus
Power supply	Rechargeable battery-powered
Weight	4.5 kg
Packaging	Modular case (HD=Heavy Duty)
Type of rechargeable battery	Lithium-ion
Quick-clamping chuck range	1.5 - 13 mm
Type of product	Hammer drill

Accessories

Battery charger Type M1218SC	073840 M1218SC
Battery charger Type M1218C	073840 M1218C
Battery starter set Type M18NRG5	073839 M18NRG5
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1418C6	073840 M1418C6