

**Cordless ratchet, Type: M12FHIR14****Order data**

Order number	070228 M12FHIR14
GTIN	4058546341046
Item class	03L

**Description****Version:****MILWAUKEE – cordless right angle drill and ratchet**

- **REDLINK™ electronics with stepless speed control, reversible running and overload protection.**
- **LED illumination of the working area.**
- **Red Li-ion batteries with single-cell monitoring and charge display.**

Compact high-speed cordless ratchet screwdriver with sensitive speed controller.

**Supplied with:****Without battery and without charger.****Note:**

See No. 073814 and No. 073839 for suitable batteries and chargers.

**Technical description**

typical application	Strong
maximum speed 1st speed	0 - 450 min <sup>-1</sup>
Weight	1 kg

Number of rechargeable batteries contained	0
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Battery capacity	2 Ah
Battery voltage	12 V
Format	Impact ratchet
maximum torque hard	47 Nm
Manufacturer's designation	M12FHIR14
Toolholder	Square 1/4 inch
maximum vibration to EN	<2,5 m/s <sup>2</sup>
Type of rechargeable battery	Lithium-ion
Type of product	Screwdriver

## Accessories

Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
--	-------------