

AEG

Cordless compact combi drill, Type: BSB18C2X24



Order data

Order number	070229 BSB18C2X24
GTIN	4058546287528
Item class	07A

Description

Version:

2-Speed cordless impact drill screwdriver with brushless motor.

- **Electronic speed control for smooth, safe starts to drilling and screw driving; reversible.**
- **2-speed all-metal gearbox with selectable hammer drive in metal, stone and masonry.**
- **Multi-stage torque adjustment and removable drill chuck.**

Compact and powerful 18V cordless impact wrench for the most demanding applications.

Supplied with:

1 × 18 V/ 2.0 Ah and 1 × 18 V/ 4.0 Ah PRO Li-ion batteries, 1 × charger, carrying case.

Note:

See No. 073820, 073841 and 073842 for suitable batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: AEG type B 18 V

Manufacturer's designation: BSB 18C2XLI-X02C

Number of rechargeable batteries contained: 2

Type of rechargeable battery: Lithium-ion

Battery capacity: 2 A·h

Battery capacity: 4 A·h

Battery voltage: 18 V

Technical description

typical application	Heavy Duty
maximum twist drill size Ø in wood	45 mm
maximum torque hard	50 N·m
maximum torque hard	60 N·m
suitable battery - supplier / battery type / voltage	AEG type B 18 V
Number of rechargeable batteries contained	2
maximum torque soft	32 N·m
maximum vibration to EN with hammer drill function	13 m/s ²
Battery capacity	2 A·h
Battery capacity	4 A·h
Type of rechargeable battery	Lithium-ion
maximum vibration to EN without hammer drill function	< 2.5 m/s ²
maximum speed 2nd speed	1800 min ⁻¹
Quick-clamping chuck range	1.5 - 13 mm
Motor design	Brushless
Battery voltage	18 V
maximum twist drill size Ø in steel	13 mm
Manufacturer's designation	BSB 18C2XLI-X02C
Weight	1.7 kg
maximum speed 1st speed	0 - 450 min ⁻¹
Packaging	Carrying case
Power supply	Rechargeable battery-powered
maximum twist drill size Ø in concrete	14 mm
Type of product	limpact drill /screwdriver