

Garant
Centring vice, pneumatic, Type: 100

Order data

Order number	360180 100
GTIN	4062406572945
Item class	310

Description
Version:

- **Adjustable stroke + 5 mm per end.**
- **Clamping force steplessly adjustable up to 22.5 kN. Arithmetical sum = 45 kN.**
- **Even if the compressed air supply fails, the centring vice maintains a slight (approx. 60 kg) pre-load, to ensure secure positioning of the workpiece, such as when a shuttle table is being used.**

Application:

For centralised clamping of components. Suitable for **automated operation** with 4-channel clamping pots, even with side connections.

Optional extras:

Range of jaws no. 360135 - 360151 size 80.

Technical description

Maximum compressed air supply	9 bar
Height H	95 mm
L	100 mm
Jaw width A	80 mm

Weight	4.8 kg
Clamping range	6 mm
Clamping force up to maximum	10 kN
B	100 mm
suitable for colour code	PCV 100
Type of product	Machine vice