

Garant GRIDLINE

Set of troughs, 36×14G, Drawer front height / type: 50/2



Order data

Order number	950197 50/2
GTIN	4062406573553
Item class	9GB

Description

Version:

Troughs and divider plates of plastic. Troughs slotted on the inside for division using divider plates.

Dividing material fills a complete drawer 36×14G.

Suitable for:

Drawers 36×14G.

Content:

Troughs 1K No. 951415: 6 pcs. size 6×8/3; 6 pcs. size 6×6/3

Troughs divider plates (10 pcs.) No. 951275: 4 × size B

Technical description

Trough height	25 mm
suitable for drawers usable width	900 mm
Material	Plastic
suitable for drawers usable depth in G	14
suitable for drawers usable width in G	36
suitable for drawers usable depth	350 mm
Drawer usable area in G	36×14
suitable for drawer front height	50 mm
suitable for drawer front height	100 mm

suitable for drawer front height	75 mm
suitable for drawer front height	150 mm
suitable for drawer front height	125 mm
suitable for drawer front height	250 mm
suitable for drawer front height	200 mm
suitable for drawer front height	300 mm
suitable from drawer front height	≥ 50 mm
Width	900 mm
Depth	350 mm
Width in G	36
Depth in G	14
Height	25 mm
Weight	1.31 kg
Product name attribute	36×14G
Type of product	Drawer trough

Accessories

Trough divider plates Set 10 pieces Type B	951275 B
Trough height 25 mm 1K Width×depth in G / type 6X6/3	951415 6X6/3
Trough height 25 mm 1K Width×depth in G / type 6X8/3	951415 6X8/3