

Garant**Flap wheel Fleece (ZA), disc-shaped, medium, Head Ø×head width: 60X50mm****Order data**

Order number	554940 60X50
GTIN	4062406573713
Item class	51E

Description**Version:**

Especially wear-resistant and fine-structured fleece with Zirconium Aluminium Oxide (ZA). **Ideal for use on stainless steel.** Shank Ø 6 mm.

Application:

Highly recommended for sanding contoured surfaces.

Technical description

recommended speed	4000 min ⁻¹
Shank Ø	6 mm
Head width	50 mm
Head Ø	60 mm
maximum speed	7000 min ⁻¹
Grinding media	Zirconium abrasive (ZA)
Grinding medium code	ZA
Grit equivalent	180
Grit designation	medium

Product name attribute	medium
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		