

Garant GRIDLINE

ESD Vario workbench with casing, height 850 mm, ESD worktop, 12×20G, Worktop length: 1500/5mm



Order data

Order number	972152 1500/5
GTIN	4062406573454
Item class	9GG

Description

Version:

Workbench in sturdy steel construction. Support legs 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With 1 pair of stabilising plates for stiffening. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Worktop made of 50 mm volume-conductive chipboard. Surface coating made of conductive HPL plastic ESDS 0.8 mm. Underside with counter-balance made of white laminated plastic. All-round 3 mm antistatic ABS edge band. With internal steel tube as reinforcement profile.

Fitted with:

Drawer front height, mm: 75, 75, 75, 75, 125

Supplied with:

2 × support legs, 1 × pair of stabilising plates, drawer cabinet with drawers, worktop.

Colour:

Casing and supports light grey similar to RAL 7035, **ESD powder-coated.**

Note:

Central hole for grounding plug No. 972827 size INT2W on the underside of the ESD worktop. Grounding plug must be ordered separately.

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Number of drawers	5
-------------------	---

Drawer usable depth	500 mm
Series	vario
Height	850 mm
Drawer usable depth in G	20
Drawer body depth	650 mm
Drawer body usable height	425 mm
Drawer usable width	300 mm
Drawer body width	400 mm
Drawer usable area in G	12×20
Drawer usable width in G	12
Worktop depth	750 mm
Worktop length	1500 mm
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Drawer body height	500 mm
Worktop thickness	50 mm
Design version	Steel hollow section construction
Workbench height	850 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Product name attribute	12×20G
Type of product	Workbench

Accessories

Lock plate for GridLine Type KO21	914227 KO21
-----------------------------------	-------------

ESD casing 16G for individual configuration with drawers Height of the housing 500 mm	972030 500
ESD drawer Drawer front height 75 mm	972035 75
ESD drawer Drawer front height 125 mm	972035 125
ESD worktop Worktop length 1500 mm	972160 1500
ESD support leg Number of pull-out frames 800 mm	972180 800
Stabilising plate Type 1	972195 1