

**Carbide-tipped multi-purpose drill, 1/4 inch (E 6.3), Drill Ø: 12mm****Order data**

Order number	787001 12
GTIN	4058546287382
Item class	76G

**Description****Version:**

Carbide tip **with ground point and multi-purpose cutter angle**. The **centrally ground chisel edge** ensures accurate spot drilling also on hard surfaces. Shank of annealed special steel.

**Application:**

For drilling various materials, in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass**
- **Reinforcing bars in concrete.**

**Note:**

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

**Technical description**

Drill Ø	12 mm
Flute length	90 mm
overall length	150 mm
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Bit hexagon shank	E 6.3
Type of product	Multi-purpose drill

