



Carbide-tipped multi-purpose drill, 1/4 inch (E 6.3), Drill Ø: 5mm



Order data

Order number	787001 5
GTIN	4058546287214
Item class	76G

Description

Version:

Carbide tip **with ground point and multi-purpose cutter angle**. The **centrally ground chisel edge** ensures accurate spot drilling also on hard surfaces. Shank of annealed special steel.

Application:

For drilling various materials, in a single operation:

- **Bricks, porous concrete, lightweight materials, plastics.**
- **Tiles, ceramics, marble, glass**
- **Reinforcing bars in concrete.**

Note:

- **Caution: only for rotary use (without hammer action!)**
- **Faster drilling and more holes per battery charge than with hammer drill bits.**

Technical description

Flute length	50 mm
Drill Ø	5 mm
overall length	100 mm
Tool material	Carbide
Use with impact / without impact	not for impact drilling
Bit hexagon shank	E 6.3
Type of product	Multi-purpose drill

