

Garant**Pair of gloves MASTER FIT, Glove size: 12****Order data**

Order number	094305 12
GTIN	4062406573959
Item class	01H

Description**Version:**

Anatomically shaped multi-purpose gloves with two-piece coating of nitrile and nitrile foam, with water-based PU. Particularly pleasant backing material with **18-gauge knitted technology** of nylon for outstanding tactile sensitivity. Suitable both for dry working environments and for oily, greasy and wet areas. Free of DMF.

Standard:

EN 388, EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Series	MASTER FIT
Protection category	Category II
Type of glove	Multi-purpose gloves
Clothing standard	Oeko-Tex Standard 100

Glove characteristics	DMF-free
EN 388	4121X
Backing material	Nylon
Coating	Nitrile/PU
Coating variant	The palms of the hands
Application range	All-round
Application range	Precision
Length	250 mm
Colour	blue / orange
Knitted technology	18G
Application	reusable
Type of product	Multi-purpose gloves