

Garant**Pair of gloves MASTER FIT OIL, Glove size: 12****Order data**

Order number	094307 12
GTIN	4062406574017
Item class	01H

Description**Version:**

Multi-purpose gloves with **18-gauge knitted technology** and a double coating of nitrile and sanded nitrile. The structured surface on the palm of the hand and fingers ensures a very good grip under oily conditions. Free of DMF.

MASTER FIT OIL. With 3/4 nitrile coating over the knuckles. Makes the gloves extremely suitable for wet and oily working environments.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	12
Protection category	Category II
Series	MASTER FIT
Type of glove	Multi-purpose gloves

Clothing standard	Oeko-Tex Standard 100
Glove characteristics	DMF-free
EN 388	4121X
Backing material	Nylon
Coating	Nitrile
Coating variant	3/4 coating
Application range	All-round
Application range	Precision
Length	250 mm
Colour	blue / orange
Knitted technology	18G
Application	reusable
Type of product	Multi-purpose gloves