

Mitutoyo**Projector with screen and lens PJ-PLUS, Type: P2010A****Order data**

| | |
|--------------|---------------|
| Order number | 493513 P2010A |
| GTIN | 4946368848211 |
| Item class | 44C |

Description**Version:**

Projector for the exact transillumination and incident light inspection of small to medium-sized components. **Universal tool** for use in production, laboratories, inspection, and grinding shops.

- **Standard lens 10x. 20x, 50x and 100x magnification lenses on request.**
- **Vertical, rotating 315 mm cross hair screen with built-in digital angle display, changeover function for reading in degrees or decimal.**
- **The telecentric lighting system guarantees a vertical and even illumination of the image field.**
- **LED transillumination and incident lighting with stepless light intensity control ensure a long service life with low power consumption.**
- **Fanless design prevents the ingress of contamination into the unit.**
- **Sturdy coordinate measurement table, with quick adjustment in both axes.**
- **Built-in digital display (with data output) guarantees reliable, error-free measuring.**
- **For measuring lengths, angles, curves, and radii.**

Supplied with:

Incl. lens 10x magnification, anti-glare, cover, and mains lead.

Optional extras:

Cutting edge cleaner No. 354788.

Note:

Further special accessories such as lenses, tilting central support, horizontal Vee, toolholder, standard comparison scales or an edge sensor with QM-Data 200 analysis unit available on request.

Technical description

| | |
|--------------------------|----------------|
| Height | 1093 mm |
| Weight | 118 kg |
| Width | 633 mm |
| Scale divisions | 0.001 mm |
| Series | PJ-PLUS |
| Screen Ø | 315 mm |
| maximum component weight | 8 kg |
| Measuring range, y-axis | 100 mm |
| Power supply | Mains operated |
| Length | 742 mm |
| Measuring range x-axis | 200 mm |
| digital display | yes |
| Lighting | LED |
| Type of product | Shadowgraph |