

HEDI

All-plastic cable drum for F, B, PL and CZ, Type: 50B



Order data

Order number	081109 50B
GTIN	4003644023554
Item class	08B

Description

Version:

HEDI® cable drums stand for "Made in Germany" quality and a long service life. The drum body is specially designed to optimally guide the cable. The integrated rotation stop switch prevents accidental rotation of the drum. All cable drums are equipped with thermal cut-out switches.

Large, high-quality HEDI® all-plastic cable reel with a reel diameter of 290 mm and numerous ergonomic and safety features.

- **Inclined 7 degrees for greater ground clearance and to make it comfortable to carry.**
- **Removable cable holder and guide for optimum cable control.**
- **Water drainage grooves.**
- **Twist grip for individual right-hand and left-hand operation when winding or unwinding the cable.**
- **Easy to mount on a wall.**
- **Certified for continuous exterior use and for use in humid environments.**

With sockets for **France, Belgium, Poland and the Czech Republic.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Technical description

Cable colour	orange
Power supply	Mains operated
Number of sockets	4
Cable length	50 m
Nominal voltage	250 V
impact-resistant and splash-proof	Category 2 (K2) to BGI
suitable for countries	F, B, PL, CZ
Cable structure	3G1.5
Cable class	H07BQ-F
IP Index of Protection	IP 54
Rated power unrolled	3500 (16 A) W
Material cable	Armoured cable
Diagnostic system present	yes
Type of product	Cable drum