



Cordless stapler, Manufacturer's designation: M12BST



Order data

Order number	078403 M12BST
GTIN	4058546028060
Item class	03L

Description

Version:

Compact and powerful M12™ **cordless stapler** with integral staple insertion slide and non-slip grip. Up to 2000 staples per 2.0 Ah battery charge. Function to prevent accidental operation.

Suitable for:

Type G staples with maximum insertion depth of 6–14 mm.

Supplied with:

Version **without rechargeable battery, without charger, without HD box.**

Technical description

Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	0
Power supply	Rechargeable battery-powered
suitable type of staple	G
Manufacturer's designation	M12BST
Battery voltage	12 V

maximum staple insertion depth	14 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Packaging	cardboard
Type of product	Tacker

Accessories

Li-ion system M4B2/M12B2 Battery type MB12	073814 MB12
Battery charger Type M1218C	073840 M1218C