

**Non-slip floor marking tape 0.72 mm thick, Type: B/Y****Order data**

| | |
|--------------|---------------|
| Order number | 964970 B/Y |
| GTIN | 4042448841957 |
| Item class | 97M |

Description**Version:**

Self-adhesive floor marking tape tesa® **non-slip tape 60950-60953** for indoor and outdoor use. Very strong adhesive strength on many substrates, resistant to salt water and chemicals. Adhesive tapes consist of a PVC backing coated with mineral particles (aluminium oxide). Permanent non-slip effect of up to 2 years under normal use.

Standard:

DIN 51130, DIN 67510.

Technical description

| | |
|----------------------------|--------------------|
| Special features | tearable by hand |
| Special features | moisture-resistant |
| Length | 15 m |
| Application | Marking |
| Adhesive strength on steel | 100 N/mm |
| Width | 50 mm |

| | |
|-----------------------------|--------------------|
| Colour | black / yellow |
| Stretch capability | 25 % |
| Thickness | 0.81 mm |
| Type of adhesive tape | single-sided |
| Backing material | PVC film |
| Adhesive | Acrylate |
| temperature-resistant up to | -5 - 50 °C |
| Type of product | Floor marking tape |