



## Diamond burnishing tips, Tip radius: 0,6mm



### Order data

Order number	291410 0,6
GTIN	
Item class	29M

### Description

**Advantage:**

Thanks to indexing there are 8 possibilities for using the diamond burnishing tips.  
Surface quality  $R_z < 1 \mu\text{m}$  possible.

**Application:**

For machining materials up to 65 HRC. Ideal for machining the surfaces of complex, continuous contours.

**Accuracy:**

Surface quality  $R_z < 1 \mu\text{m}$  possible.

**Note:**

For detailed application recommendations please see the instruction handbook supplied.  
Use the largest possible radius.

### Technical description

Tip radius	0.6 mm
Type of product	Smooth rolling tool