

**Garant**
**GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank  $\varnothing$  / insert size: 8/06mm**

**Order data**

Order number	260030 8/06
GTIN	4062406575731
Item class	21T

**Technical description**

Head length $L_1$	20 mm
Pack of insert screws	269028 7
Centre offset $L_3$	5 mm
Overall length $L$	100 mm
Minimum pre-drill $\varnothing D_{\min}$	10 mm
suitable indexable insert	CC.. 0602..
Shank $\varnothing D_s$	8 mm
Insert size	6 mm
Clamping height $L_2$	7 mm
ISO code toolholder	A08H SCLCR/L06
Series	GARANT Master
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar