

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 10/06mm

Order data

Order number	260030 10/06
GTIN	4062406575748
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	12 mm
suitable indexable insert	CC.. 0602..
Centre offset L_3	6 mm
Shank $\varnothing D_s$	10 mm
Series	GARANT Master
Pack of insert screws	269028 7
Overall length L	125 mm
ISO code toolholder	A10K SCLCR/L06
Insert size	6 mm
Head length L_1	20 mm
Clamping height L_2	9 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar