

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 12/06mm

Order data

Order number	260030 12/06
GTIN	4062406575755
Item class	21T

Technical description

Clamping height L_2	11 mm
Insert size	6 mm
Shank $\varnothing D_s$	12 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	A12L SCLCR/L06
Overall length L	140 mm
Pack of insert screws	269028 7
Series	GARANT Master
Centre offset L_3	7 mm
Minimum pre-drill $\varnothing D_{min}$	14 mm
Head length L_1	24.3 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar