

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank Ø / insert size: 25/12mm

Order data

Order number	260030 25/12
GTIN	4062406575793
Item class	21T

Technical description

ISO code toolholder	A25R SCLCR/L12
Head length L ₁	43 mm
Overall length L	200 mm
Series	GARANT Master
Insert size	12 mm
Pack of insert screws	269028 9
suitable indexable insert	CC.. 1204..
Minimum pre-drill Ø D _{min}	27 mm
Clamping height L ₂	23 mm
Centre offset L ₃	13.5 mm
Shank Ø D _s	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar