

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 16/09mm

Order data

Order number	260030 16/09
GTIN	4062406575762
Item class	21T

Technical description

Head length L_1	31 mm
Centre offset L_3	9 mm
Shank $\varnothing D_s$	16 mm
Overall length L	180 mm
Minimum pre-drill $\varnothing D_{min}$	18 mm
Series	GARANT Master
suitable indexable insert	CC.. 09T3..
Pack of insert screws	269028 8
Clamping height L_2	15 mm
Insert size	9 mm
ISO code toolholder	A16Q SCLCR/L09
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar