

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 20/09mm

Order data

Order number	260030 20/09
GTIN	4062406575779
Item class	21T

Technical description

Clamping height L_2	18 mm
Series	GARANT Master
Shank $\varnothing D_s$	20 mm
Minimum pre-drill $\varnothing D_{min}$	22 mm
Pack of insert screws	269028 8
Overall length L	200 mm
suitable indexable insert	CC.. 09T3..
ISO code toolholder	A20R SCLCR/L09
Centre offset L_3	11 mm
Head length L_1	36 mm
Insert size	9 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar