

**Garant**
**GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank Ø / insert size: 8/06mm**

**Order data**

Order number	260031 8/06
GTIN	4062406573768
Item class	21T

**Technical description**

Minimum pre-drill Ø $D_{min}$	10 mm
ISO code toolholder	A08H SCLCR/L06
Series	GARANT Master
Centre offset $L_3$	5 mm
suitable indexable insert	CC.. 0602..
Clamping height $L_2$	7 mm
Head length $L_1$	20 mm
Overall length $L$	100 mm
Pack of insert screws	269028 7
Insert size	6 mm
Shank Ø $D_s$	8 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar