

**Cordless angle grinder GWS, Type: 18V-7****Order data**

Order number	077120 18V-7
GTIN	3165140978637
Item class	03C

Description**Version:**

Extremely powerful 18 V cordless angle grinder in compact design.

Supplied with:

Without rechargeable battery and charger, including safety guard, mounting flange, clamping nut, additional handle.

Note:

See No. 073854 and No. 073866 for suitable spare batteries and chargers.

Technical description

Soft start	no
maximum vibration to EN	7 m/s ²
Dead man's circuit	no
Manufacturer's designation	GWS 18V-7
maximum cutting depth	34 mm
Battery voltage	18 V
Packaging	Modular case (L-Boxx)
Type of rechargeable battery	Lithium-ion
maximum disc Ø	125 mm

suitable battery - supplier / battery type / voltage	Bosch 18 V
Number of rechargeable batteries contained	0
maximum speed	11000 min ⁻¹
Kick-back stop	no
Weight	2.3 kg
Overload protection	yes
Power supply	Rechargeable battery-powered
Restart block	yes
Type of product	Angle grinder