

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank Ø / insert size: 16/09mm

Order data

Order number	260031 16/09
GTIN	4062406576721
Item class	21T

Technical description

Centre offset L_3	9 mm
Overall length L	180 mm
Series	GARANT Master
Minimum pre-drill $\varnothing D_{\min}$	18 mm
Pack of insert screws	269028 8
ISO code toolholder	A16Q SCLCR/L09
Clamping height L_2	15 mm
Shank $\varnothing D_s$	16 mm
suitable indexable insert	CC.. 09T3..
Head length L_1	31 mm
Insert size	9 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar