

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 25/12mm

Order data

Order number	260031 25/12
GTIN	4062406576752
Item class	21T

Technical description

Insert size	12 mm
Overall length L	200 mm
Pack of insert screws	269028 9
Minimum pre-drill $\varnothing D_{\min}$	27 mm
Clamping height L_2	23 mm
Head length L_1	43 mm
Shank $\varnothing D_s$	25 mm
Series	GARANT Master
suitable indexable insert	CC.. 1204..
Centre offset L_3	13.5 mm
ISO code toolholder	A25R SCLCR/L12
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar