

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	260337 10/07
GTIN	4062406576820
Item class	21T

Technical description

Series	GARANT Master
Centre offset L_3	7 mm
Clamping height L_2	9 mm
Head length L_1	20 mm
suitable indexable insert	DC.. 0702..
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Pack of insert screws	269028 7
Overall length L	125 mm
Insert size	7 mm
ISO code toolholder	A10K SDUCR/L07
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar