

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	260336 12/07
GTIN	4062406576776
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
Shank \varnothing D_s	12 mm
Centre offset L_3	8 mm
Overall length L	140 mm
Pack of insert screws	269028 7
Head length L_1	25 mm
Minimum pre-drill \varnothing D_{min}	15 mm
ISO code toolholder	A12L SDUCR/L07
Insert size	7 mm
Series	GARANT Master
Clamping height L_2	11 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar