

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 25/11mm

Order data

Order number	260336 25/11
GTIN	4062406576813
Item class	21T

Technical description

Shank \varnothing D _s	25 mm
suitable indexable insert	DC.. 11T3..
Head length L ₁	40 mm
Series	GARANT Master
Insert size	11 mm
Pack of insert screws	269028 8
Overall length L	200 mm
ISO code toolholder	A25R SDUCR/L11
Minimum pre-drill \varnothing D _{min}	31 mm
Clamping height L ₂	23 mm
Centre offset L ₃	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar