

**Garant**
**GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	260337 12/07
GTIN	4062406576837
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	15 mm
Pack of insert screws	269028 7
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Centre offset $L_3$	8 mm
Head length $L_1$	25 mm
Clamping height $L_2$	11 mm
Series	GARANT Master
ISO code toolholder	A12L SDUCR/L07
Shank $\varnothing D_s$	12 mm
Overall length L	140 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar