

Garant
GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank \varnothing / insert size: 10/07mm

Order data

Order number	260336 10/07
GTIN	4062406576769
Item class	21T

Technical description

Centre offset L_3	7 mm
Shank $\varnothing D_s$	10 mm
suitable indexable insert	DC.. 0702..
Head length L_1	20 mm
Series	GARANT Master
Pack of insert screws	269028 7
Insert size	7 mm
ISO code toolholder	A10K SDUCR/L07
Clamping height L_2	9 mm
Minimum pre-drill $\varnothing D_{min}$	13 mm
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar