

**Garant**
**GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank  $\varnothing$  / insert size: 20/11mm**

**Order data**

Order number	260337 20/11
GTIN	4062406576868
Item class	21T

**Technical description**

Clamping height $L_2$	18 mm
Series	GARANT Master
Pack of insert screws	269028 8
Overall length $L$	200 mm
Head length $L_1$	36 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Insert size	11 mm
Shank $\varnothing D_s$	20 mm
Centre offset $L_3$	13 mm
ISO code toolholder	A20R SDUCR/L11
suitable indexable insert	DC.. 11T3..
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar