

**Garant**
**GARANT Master Turn boring bar, steel spiral flutes, right-hand, Shank  $\varnothing$  / insert size: 10/07mm**

**Order data**

Order number	260330 10/07
GTIN	4062406576882
Item class	21T

**Technical description**

ISO code toolholder	A10K SDQCR/L07
Shank $\varnothing$ D <sub>s</sub>	10 mm
Centre offset L <sub>3</sub>	7 mm
Overall length L	125 mm
Clamping height L <sub>2</sub>	9 mm
Series	GARANT Master
Minimum pre-drill $\varnothing$ D <sub>min</sub>	13 mm
Head length L <sub>1</sub>	20 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

