

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 25/11mm

Order data

Order number	260337 25/11
GTIN	4062406576875
Item class	21T

Technical description

Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Series	GARANT Master
Head length L_1	40 mm
ISO code toolholder	A25R SDUCR/L11
Centre offset L_3	16 mm
Shank $\varnothing D_s$	25 mm
Overall length L	200 mm
Clamping height L_2	23 mm
Minimum pre-drill $\varnothing D_{min}$	31 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar