

Garant
GARANT Master Turn boring bar, steel spiral flutes, left-hand, Shank \varnothing / insert size: 16/11mm

Order data

Order number	260337 16/11
GTIN	4062406576851
Item class	21T

Technical description

Series	GARANT Master
Overall length L	180 mm
Pack of insert screws	269028 8
Head length L_1	28 mm
Shank $\varnothing D_s$	16 mm
ISO code toolholder	A16Q SDUCR/L11
Centre offset L_3	14 mm
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Minimum pre-drill $\varnothing D_{min}$	23 mm
Clamping height L_2	15 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar